




MATERIAL NO.	ENG. NO.	STUD SIZE	"S" MAX	DESCRIPTION
192030492	C-S-140-38	3/8	.416/10.57	LOOSE
192030292	C-S-140-38T	3/8	.416/10.57	TAPE

NOTE(S):

1. MATERIAL: STEEL
2. WIRE SIZE: 12-10 AWG (4.0-6.0 MM²)
3. FINISH: NICKEL PLATING
4. PART IS ROHS COMPLIANT.
5. AMBIENT OPERATING TEMPERATURE UP TO 900 °F (483 °C).

ADDED OPERATING TEMP EC NO: ETC2007-0297 2007/03/13 DRW:EHILE CHKD: JMACNEIL APPR: JMACNEIL 2007/03/14	QUALITY SYMBOLS ▽=0 ◻=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
			mm	INCH	DRAWN BY EHILE	DATE 2006/09/22	TITLE RING TONGUE TERMINAL, 12-10 AWG, KRIMPTITE, 900 DEG F (483 DEG C) MOLEX INCORPORATED		
			4 PLACES ± ---	± ---	CHECKED BY JMACNEIL	DATE 2006/09/22			
			3 PLACES ± ---	± ---	APPROVED BY JMACNEIL	DATE 2006/09/22			
			2 PLACES ± ---	± ---	MATERIAL NO. SEE CHART				
1 PLACE ± ---	± ---	ANGULAR ± ---°		DOCUMENT NO. SD-19203-035		SHEET NO. 1 OF 1			
B	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		