

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202330001

Status:

Active

Overview:

Brad M23 Signal and Power Connectors

Description:

Brad M23 Power Connector, Straight Female, Crimp Contacts, 6 (5+PE) Poles, Cable Diameter 7.00-12.00mm



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	120233
Application	Power
Comments	Crimp Range 0.75-2.50mm2
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301316
Physical	
Cable Diameter	7.00-12.00mm (.276-.472")
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	Straight
Poles	6 (5+PE)
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	28.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	KAP6S00-105
Reference - Drawing Numbers	
Sales Drawing	SD-120233-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

120233 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION