

RAD-CAB-EF393-10M

Order No.: 2867665

The illustration shows a version of the product



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867665>

Antenna cable, 10 m in length; N (male) -> N (male), attenuation approx. 0.45 dB/m at 2.4 GHz; impedance 50 ohms

Commercial data

GTIN (EAN)	 4 017918 939038
sales group	H178
Pack	1 pcs.
Customs tariff	85442000
Catalog page information	Page 623 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
09/03/2007



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General

Connection 1	Plug connector connection
Type of connection	Type N (male)
Fixed cable length	10 m
Cable type	EF 393
Cable, attenuation	approx. 0.45 dB/m

Minimum bending radius	50.00 mm
External diameter	10.00 mm
Outer sheath, material	Radox (LSFH)
Connection name	Plug connector connection
Type of connection	Type N (male)
Note	Both sides
Ambient temperature (operation)	-40 °C ... 105 °C

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;