

TUNING ROTOR

SPECIFICATIONS		FILE: AIROUT
PRE-TORQUED AND LUBRICATED THREADS		
FINISH	JOHANSON STANDARD CHROMATE CONVERSION	
MOUNTING	JMC TAP P/N 7059 (.156-64 UNS-2)	
BRASS STRUCTURE		
APPLICATIONS: FOR HIGH Q VARIABLE REACTANCE TUNING OF MICROWAVE CAVITIES, FILTERS, AND OTHER RESONANT STRUCTURES		

FIG.1




FIG.2





FIG.3



NOTE: TYPICAL THREAD SIZE, 5/32(.156)-64 UNS-2A

PART NO.	FIG.	A ^{+.000} _{-.020}	B	C
L6996-0	1	.227	.125	.062
L6996-1	1	.250	.148	.125
L6996-2	1	.380	.278	.125
L6996-3	1	.552	.450	.125
L6996-4	1	.125	.023	.125
L6996-5	1	.295	.193	.125
L6996-6	1	.180	.078	.125
L6996-7	2	.117	.015	.125
L6996-8	1	.192	.090	.125
L6996-9	3	.250	.148	.125
L6996-11	1	.432	.330	.125
L6996-12	1	.190	.088	.062
L6996-13	1	.470	.368	.125
L6996-16	1	.168	.066	.125
L6996-17	1	.148	.046	.125

M	01/26/04	MLD	-	-	000073
LEVEL	DATE	DRN.	CHK.	APP.	ECN
REVISIONS					
DRN.	MLD	CHK.	RJV	APP.	JHT
DATE	DATE	DATE	DATE	DATE	SCALE
01/26/04	02/02/04	02/04/04	02/04/04	02/04/04	4" = 1"
					.XX ± .015
					.XXX ± .005



JOHANSON MANUFACTURING CORPORATION
ROCKAWAY VALLEY ROAD, BOONTON, N.J. 07005 (973)334-2676 FAX (973)334-2954
ELECTRONIC ACCURACY THROUGH MECHANICAL PRECISION