

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130048-0126](#)
Status: **Active**
Overview: [industrial_ethernet_solutions](#)
Description: Micro-Change® (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 26 AWG, PVC Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Cordsets
Series [130048](#)
Connector End A Micro-Change® (M12)
Connector End B Micro-Change® (M12)
IP Rating IP67
Overview [industrial_ethernet_solutions](#)
Performance Category 5e
Product Name Micro-Change® (M12)
Protocol Ethernet
Region America, Asia, Europe
Type Double Ended
UPC 78678803804

Physical

Cable Diameter 5.59mm (.220")
Cable Length 5.0m (16.40')
Color - Cable Jacket Teal
Coupling Style Threaded
Gender Male-Male
Keyway D-coded
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Contact Copper Alloy
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Net Weight 270.390/g
Orientation Straight
Poles 4
Temperature Range - Operating -20°C to +75°C
Wire Size AWG 26
Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 1.5A
Voltage - Maximum 30V

Material Info

Old Part Number E11A06015M050

Reference - Drawing Numbers

Sales Drawing SD-120108-020, SD-130048-006



Series

image - Reference only

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130048Series](#)

This document was generated on 12/01/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION