


DESIGNED TO MEET NEMA 1, 2, 4, 4X, 12, 13 AND IP-66
UL LISTED AND TESTED TO UL508A. UL FILE #E194432




MATERIAL:

BODY & COVER - 16 GA. [1.5mm] TYPE 304 STAINLESS STEEL
INTERNAL PANEL - 14 GA. [2.0mm] C.R.S.
WALL MOUNTING BRACKETS - 14 GA. [2.0mm] TYPE 430 STAINLESS STEEL
STRIKERS - 11 GA. STAINLESS STEEL 304
HINGE PINS & WALL MOUNTING HARDWARE - TYPE 201 STAINLESS STEEL
INTERNAL PANEL MOUNTING HARDWARE & GROUND STUD
HARDWARE - PLAIN STEEL
LATCHES - STAINLESS STEEL
LATCH GASKET WASHER - BLACK ACRYLONITRILE-BUTADIENE RUBBER
POURED GASKET - BLACK POLYURETHANE FOAM
SEALING WASHERS - BLACK NEOPRENE
HOLE PLUGS - LIGHT GRAY NEOPRENE

FINISH:

BODY & COVER - NATURAL, OUTSIDE SURFACES POLISHED
INTERNAL PANEL, INTERNAL PANEL MOUNTING HARDWARE
& GROUND STUD HARDWARE - CLEAR ZINC PLATED
WALL MOUNTING BRACKETS, STRIKERS & HINGE PINS - NATURAL



SUPPLIED WALL MOUNTING BRACKET KIT CONTAINS:

QTY. (4) WALL MOUNTING BRACKETS
QTY. (4) HEX HEAD BOLT M10x1.5 PITCH x 19.5mm LG.
QTY. (8) SEALING WASHERS
QTY. (4) FLAT WASHERS M10
QTY. (4) SPLIT LOCKWASHERS M10
QTY. (4) HEX NUTS M10x1.5

SUPPLIED GROUNDING KIT CONTAINS:

QTY. (1) GROUND WIRE 14-16 GA. YELLOW/GREEN
WITH RING TERMINAL (M6) AT EACH END
QTY. (4) FLAT WASHER M6
QTY. (2) SPLIT LOCKWASHER M6
QTY. (2) HEX NUT M6x1.0