

- ### TECHNICAL SPECIFICATIONS:

Dimensions (Diameter x Depth):	52 mm x 67,1 mm
Housing:	PC/ABS, black
Audio frequency:	c. 2100 Hz
Tone type:	Continuous tone or pulse tone with approx. 1 Hz
Current consumption:	25 mA
Fixing:	Installation mounting for Ø 22,5 mm (M 22) with anti-twist device
Connection:	Connector plug with screwable connection max. 1,5 mm²

ORDER SPECIFICATIONS:



Voltage	24 V $\equiv$	115 V $\equiv$	230 V $\sim$
Continuous tone	109 000 75	109 000 77	109 000 68
Pulse tone	109 010 75	109 010 77	109 010 68

ACCESSORIES:

Bracket with protective cap (IP54)	975 109 01 (see picture on page 83)
Single surface housing	975 109 02
Double surface housing	975 109 03
Triple surface housing	975 109 04

TECHNICAL DIAGRAMS

see page 108



975 109 01

Bracket