



MTFDDAA128MAM-1J2

Global » Products & Support » Solid State Storage » Client SSD » MTFDDAA128MAM-1J2

Login or Register to

+

 Save to Workspace

✉

Orderable Parts (1)

MTFDDAA128MAM-1J2

▼

» Compare All

[See all Client SSD parts](#) | [See all RealSSD C400 Client SSD parts](#)

Specs

Production ?			
Capacity	128GB	Part Status	Production
Package	1.8 SSD	Height	5mm
MT/s	6.0 Gb/s	Voltage	3.3V
Op Temp	0C to +70C	Interface	SATA
Read	500 MB/s	Write	175 MB/s
Product Name	RealSSD C400		

- **FBGA Code:**
- **SPD Data:** none
- **MBQual Data:** none

Data Sheets (1)

C400 1.8-Inch SATA NAND Flash SSD

Download PDF

» Share

» Save to Workspace

Parts with the same data sheets (6)

» MTFDDAA128MAM-1J1

» MTFDDAA256MAM-1K1

» MTFDDAA512MAM-1K1

» MTFDDAA128MAM-1J2

Where to Buy

Contact A Rep

Need Help? Contact a sales rep to request samples, get a quote, and receive a callback.

Login or

» Find my Rep

+ Check Distributors

Overview

Documentation & Support

Sim Models & Software

FAQs

Recently Added

Date	What was added
09/2011	C400 1.8-Inch SATA NAND Flash SSD

Sim Models & Software

Title & Description	Secure	ID	Updated
---------------------	--------	----	---------

» See all Sim Models (0)

Documentation & Support

- » Case Study

» Customer Service Note

» Data Sheet

» Part Numbering Guide

» Presentation
- » Product Flyer

» Technical Marketing Brief

» Technical Note

» White Paper

FAQs

- » Is the C400 a good choice for enterprise applications?
- » Is the C400 available in an industrial temperature option?
- » Is the C400 SATA 6Gb/s SSD backward compatible with legacy SATA interface speeds?
- » The hardware in the C400 SED looks very similar to your C400 drives. What's different?
- » See all FAQs