


19" -chassis



Part no.: 10828-072


Features:

- For assembly with 19" components or individually with mounting plate
- Three rows ventilation slots in base for air inlet



Technical information:

Height	Height H	h	h1	h2	Depth D
2 U	88 mm	86 mm	57.5 mm	76.2 mm	314.5 mm



Delivery comprises: Kit, Pos. 1, 2 and 3 assembled

Item	Qty	Description
1	2	Side panel, Al extrusion, RAL 7030 at 6 U: 2 Al corner profiles 1 divider plate (steel plate)
2	1	Front frame, Al die-cast, RAL 7030, rear side with counterbores for drill holes to mount handles and front panels
3	1	Rear frame, Al die-cast, RAL 7030
4	1	Cover plate, St, 1 mm, RAL 7035, plastic-coated, with GND/earthing connection
5	1	Base plate, St, 1 mm, RAL 7035, plastic-coated, with GND/earthing connection
6	4	Case foot with anti-slip protection, PC, UL 94 V-0
7	1	Assembly kit

Note:

- Extent of delivery includes screws for fixing rear panel and front panel