






D-Sub Receptacles

152-3409, 152-3415, 152-3425, 152-3437



D-Sub Receptacles



PC Board Layout

Dimensions: mm (In.)

Mouser Stock No.	Dimensions In.			
	Pos.	A	B	C
152-3409	9	.643	.984	1.21
152-3415	15	.971	1.31	1.54
152-3425	25	1.51	1.85	2.09
152-3437	37	2.16	2.50	2.73

SPECIFICATIONS

Type:	right angle with PCB pins
Contact resistance:	30mΩ max. @ 100mA DC
Insulator resistance:	1000mΩ min. @ 500VDC
Current rating:	1A
Dielectric withstanding voltage:	500VAC for 1 minute
Operating temperature:	-55°~+105°C
Contact:	gold plated phosphor bronze
Housing:	PBT & 30% glass fiber

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300662

152-3409, 152-3415, 152-3425, 152-3437

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[152-3425](#) [152-3415](#) [152-3437](#) [152-3409](#)