




25

LOOSE PIECE, BAG

8-34176-5

4

LOOSE PIECE, BLS

8-34176-4

100

LOOSE PIECE, BOX

8-34176-1

2500

ON TAPE, REEL

2-34176-1

500

LOOSE PIECE

34176

QTY

PACKAGE TYPE

PART NO

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL

PRODUCT INFORMATION OR

COPIES OF DRAWINGS

AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER

1-800-522-6752

FOR APPLICATION

TOOLING INFORMATION

TOOLING ASSISTANCE CENTER

1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING

TEMPERATURE:

105°C [221°F]

VOLTAGE RATING:

600V MAX

(1000V FIXTURE OR SIGN)

CIRCULAR MIL AREA:

2.62-6.64mm² [5,180-13,100]

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm[INCHES]

TOLERANCES UNLESS

OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20 [.008]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL

4

DWN

G VINSON

28NOV94

CHK

M ELLIS

28NOV94

APVD

G NGO

28NOV94

PRODUCT SPEC

UL 486A

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

TERMINAL, SPADE,

PLASTI-GRIP,

WIRE SIZE:12-10 AWG

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-34176

-

SCALE

6:1

SHEET

1 OF 1

REV

J1

1470-19 (3/11)