


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

*PANDUIT PART NUMBER	A IN (mm)	B IN (mm)	T IN (mm)	WEIGHT LBS (g) / 100 FT
T38P-0	.375 (9.5)	.437±.047 (11.1±1.2)	.030±.010 (0.8±0.3)	1.28 lbs. (581 g)
T50P-0	.500 (12.7)	.500±.047 (12.7±1.2)	.030±.010 (0.8±0.3)	1.86 lbs. (844 g)
T100P-0	1.000 (25.4)	1.125±.047 (28.6±1.2)	.030±.010 (0.8±0.3)	3.90 lbs. (1769 g)

Notes;

- * 1) See current price sheet for part number suffix designations, package size and part color.
- 2) For roll sizes larger than 10ft., splicing may occur.
- 3) Reverse Cut



DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

10D009BA_DC/01A-POLYPROPYLENE_SPIRAL_WRAP

CORP. TINLEY PARK, ILLINOIS

(WEATHER RESISTANT)
POLYPROPYLENE SPIRAL WRAP
(CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	----	(.XXX) ±	----
(.XX) ±	----	ANGLES ±	----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

MAT'L:

POLYPROPYLENE

SCALE NONE

DRAWING NO.

10D009BA - DC

DWG
A
SIZE

I	5/24/11	LEF	VJS	A ADDED "•" B ADDED NOTE 3 REVERSE CUT	10D009BA	I	RAMI		
R	6/09/10	LEF	JVL	INITIAL RELEASE	10D009BA	R	RAMI		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T100P-C0](#) [T38P-C0](#) [T50P-C0](#)