






NOTE: All relevant materials are complied with RoHS directive .

|                                           |                                                     |          |          |
|-------------------------------------------|-----------------------------------------------------|----------|----------|
| 6                                         | PLASTO-VISCO-ELASTIC BODY                           | 4        | M562     |
| 5                                         | SCREW 3*6PWB                                        | 4        | M805     |
| 4                                         | METAL CASE, THICKNESS 0.8mm                         | 1set     | M415     |
| 3                                         | UL1061 26AWG INSULATOR, LENGTH 150mm                | 47       | M541     |
|                                           | MAIN HEART 2-16-2                                   | 1        | M94      |
|                                           | SCREW 4*12.5mm WITH PAD                             | 1set     | M94      |
|                                           | KNOB FOR A, B, SWITCH                               | 1        | M94      |
| 2                                         | HEX-NUT 4.75*13mm, SCREW CAP 4.75*1.5               | 6set     | M95      |
| 1                                         | HD15 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR | 3        | M108     |
| No.                                       | DESCRIPTION                                         | Q'TY     | Supplier |
| APPROVED                                  |                                                     |          |          |
| CHECKED                                   | RAN                                                 |          |          |
| DRAWING                                   | TIAN                                                | ITEM NO. | SB-472   |
| Cable Length Unless Other Spec Tolerances |                                                     |          |          |
| 0 ~0.2M ±0.01M                            |                                                     |          |          |
| 0.21~1.0M ±0.02M                          |                                                     |          |          |
| 1.1 ~1.5M ±0.025M                         |                                                     |          |          |
| 1.51~2.1M ±0.03M                          |                                                     |          |          |
| 2.1M ↑ ±0.04M                             |                                                     |          |          |

