



Sample photo

Order symbol: PCM 125/125 T
Product nbr: 6016910
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074038234
El. number:
 Finland 3421663
 Denmark 8212027132
 Italy 7342035
 Sweden 2535421

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:				Rating:
	L	W	H	
mm:	130	130	125	Ingress Protection (EN 60529): IP 66/67
inch:	5.1	5.1	4.9	Impact Resistance (EN 50102): IK 08
Materials:				Electrical insulation: Totally insulated
Material:	PC			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035			UV resistance: UL 508
Cover colour:	Smoked grey			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:	Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Black			NEMA Class: NEMA 1, 4, 4X, 6
Gasket material:	TPE			Certificates:
Temperatures:				Germanischer Lloyd (GL)
Short term:	-40 ... 120 °C			Underwriters Laboratories
Continuous:	-40 ... 80 °C			Det Norske Veritas
Short term:	-40 ... 250 °F			Fimko
Continuous:	-40 ... 175 °F			Europe EN 50298 1998
Accessories:				UL Canada
MIV 125	Mounting plate			Gost R
MIN 10	DIN-15 Mounting rail			
MIV 10	DIN-35 Mounting rail			
FP A 125/130	Front plate			
HFP 130	Front plate hinge series			

