

Value Charger

North American Region

Download Instructions and Warranty Information

[English](#) | [Français](#) | [Español](#)



Product Detail:

Designation: Value Charger

Model: CHVC2

Color: Silver

Charge Capability: "AA" (2) or (4) / "AAA" (2) or (4)
"AA" (2) and "AAA" (2) Simultaneously

Note: When charging only 2 batteries, place batteries in the two positions to the left or right.

Charging Times:
(estimated)

Battery (NiMH)	Capacity (mAh)	Estimated (time)
AA	1300-2000	8-12.5 hrs
AA	2100-2500	13-16 hrs
AAA	850-900	11-12 hrs

Shutoff Mechanism: None

Charging Current: "AA" 190mA
"AAA" 90mA

Trickle Charge: None

Input Rating: 120VAC, 60Hz

Input Power: 6W

Typical Weight: 184.3 grams (5.9 oz.)

Dimensions (mm): 132 x 70 x 57 (H x L x W)

Rev Polarity Protection: Yes

Primary Battery Detection: None

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc.

Contents herein do not constitute a warranty.

CONVENIENT

- Charges 2 or 4 NiMH AA's or AAA's



EASY

- LED Indicators



SLEEK

- Compact Design



ECONOMICAL

- Value Priced



CORDLESS

- Fold-out Plug



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer NiMH batteries.