

Half screw connection - VC-M-KV-PG16(9-13) - 1853984

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Half screw connection Pg16, made of metal, consisting of rubber seal with one hole and one pressure screw, for type 1 housings, cable [mm] 9 - 13

Key commercial data

Packing unit	1
Minimum order quantity	5
Catalog page	Page 372 (PC-2009)
GTIN	 4 017918 146313
Custom tariff number	74153300
Country of origin	POLAND

Technical data

General data

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Material, pressure screw	Nickel-plated brass
Seal material	TPE
Cable seal material	TPE
Wrench size, union nut	24 mm
Thread type on seal side	PG16
External cable diameter	9 mm ... 13 mm
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

Classifications

eclass

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109

Half screw connection - VC-M-KV-PG16(9-13) - 1853984

Classifications

etim

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441

unspsc

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 
--

Accessories

Accessories

Assembly

Half screw connection - VC-M-KV-PG21- 0 - 1854983

Half screw connection made of metal with rubber seal without hole for sealing or for individual holes