



FCIconnect.com

Copyright FCI

PRODUCT NUMBER

SEE TABLE

68617 -XXX -LF





LEAD FREE OPTION

PACKAGING OPTION NOTE 10. OMIT IF NOT REQUIRED

NO OF POSITIONS PER ROW

PLATING CODE

BASE PART NUMBER

VIEW F-F
SCALE 10/1VACUUM CAP FOR TAPE & REEL
PACKAGING OPTION. SEE NOTE 7

mat'l. code SEE NOTES 1, 3 & 8					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection  INCH/MM scale 1:1	product family DUBOX		
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title		
R	V20732	GIP		04/17/02	angles linear	.XX ±.01/0.3			SMT SINGLE ROW		
S	V21654	GIP		10/15/02		.XXX ±.005/0.13			LATCHED VCC ASSEMBLY		
T	V03-0309	HTB		04/28/03		.XXXX ±.0020/0.051					
U	V05-0463	DPU		06/28/05	dr	J. SHREINER	10/07/90	FCI 	dwg no		
V	M06-0237	MN		06/17/06	enr	M. HAHN	10/07/90		sheet 1 of 5 size		
W	M06-0433	AGS		10/31/06	chr	M. HAHN	10/07/90		68617		
X	M07-0198	MHT		4/24/07	appd	M. HAHN	10/07/90		A3		
									type		
sheet index	revision sheet	X	X	X	X	X					
		1	2	3	4	5					

form: A3

PRODUCT NO NOTE 13	PLATING CONTACT AREA NOTE 15	PLATING SOLDER TAIL	MATERIAL REF.
68617-2XX	15u"/.38u Au OR GXT MIN OVER 50u"/1.27u Ni MIN	100u"/160u" SN 2.54u"/4.06u"	NOTE 3 & 4
68617-3XX	30u"/.76u Au OR GXT MIN OVER 50u"/1.27u Ni MIN	100u"/160u" SN 2.54u"/4.06u"	NOTE 3 & 4
68617-6XX	30u"/.76u Au OR GXT MIN OVER 50u"/1.27u Ni MIN	100u"/160u" SN 2.54u"/4.06u"	NOTE 3 & 4
68617-8XX	30u"/.76u Au MIN OVER 50u"/1.27u Ni MIN	100u"/160u" SN 2.54u"/4.06u"	NOTE 3 & 4

OBSOLETE




FIGURE A
TOP ENTRY
.025/.64 SQ PIN




FIGURE B
BOTTOM ENTRY (THROUGH PWB)
.025/.64 SQ PIN


mat'l. code				surface		tolerance		projection		product family			
-				ISO 1302 ✓		ISO 406 ISO 1101				DUBOX			
ltr		ecn no dr		date		tolerances unless otherwise specified							
X						angles		linear		title			
										SMT SINGLE ROW			
										LATCHED VCC ASSEMBLY			
						0'±2'				scale 1:1			
						dr		J. SHREINER		sheet 3 of 5			
						enr		M. HAHN		size			
						chr		M. HAHN		A3			
						appd		M. HAHN		type Product Customer Drawing			
sheet index		revision sheet											



FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE



TAPE AND REEL PACKAGING ONLY

mat'l. code				surface		tolerance	projection	product family	
-				ISO 1302		ISO 406 ISO 1101		DUBOX	
ltr	ecr	no	dr	date	tolerances unless otherwise specified		INCH/MM	title	
X					angles	linear		SMT SINGLE ROW LATCHED VCC ASSEMBLY	
					0°±2'		scale 1:1	dwg no	
								sheet 4 of 5 size	
				dr	J. SHREINER	10/07/90		68617	
				enr	M. HAHN	10/07/90		A3	
				chr	M. HAHN	10/07/90		type	
				appd	M. HAHN	10/07/90		Product Customer Drawing	
sheet	revision								
index	sheet								

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO NOTE 13	NO. OF POS.	DIM C	DIM D	DIM E	TAPE & REEL PACKAGING	LF OPTION
68617-Y02	1 X 2	.100/2.54	.417/10.59	.300/7.62	NO	NOTE 13
-Y03	1 X 3	.200/5.08	.517/13.13	.400/10.16	NO	
-Y04	1 X 4	.300/7.62	.617/15.67	.500/12.70	NO	
-Y05	1 X 5	.400/10.16	.717/18.21	.600/15.24	NO	
-Y06	1 X 6	.500/12.70	.817/20.75	.700/17.78	NO	
-Y07	1 X 7	.600/15.24	.917/23.29	.800/20.32	NO	
-Y08	1 X 8	.700/17.78	1.017/25.83	.900/22.86	NO	
-Y09	1 X 9	.800/20.32	1.117/28.37	1.000/25.40	NO	
-Y10	1 X 10	.900/22.86	1.217/30.91	1.100/27.94	NO	
-Y11	1 X 11	1.000/25.40	1.317/33.45	1.200/30.48	NO	
-Y12	1 X 12	1.100/27.94	1.417/35.99	1.300/33.02	NO	
-Y13	1 X 13	1.200/30.48	1.517/38.53	1.400/35.56	NO	
-Y14	1 X 14	1.300/33.02	1.617/41.07	1.500/38.10	NO	
-Y15	1 X 15	1.400/35.56	1.717/43.61	1.600/40.64	NO	
-Y16	1 X 16	1.500/38.10	1.817/46.15	1.700/43.18	NO	
-Y17	1 X 17	1.600/40.64	1.917/48.69	1.800/45.72	NO	
-Y18	1 X 18	1.700/43.18	2.017/51.23	1.900/48.26	NO	
-Y19	1 X 19	1.800/45.72	2.117/53.77	2.000/50.80	NO	
-Y20	1 X 20	1.900/48.26	2.217/56.31	2.100/53.34	NO	
-Y21	1 X 21	2.000/50.80	2.317/58.85	2.200/55.08	NO	
-Y22	1 X 22	2.100/53.34	2.417/61.39	2.300/58.42	NO	
-Y23	1 X 23	2.200/55.88	2.517/63.93	2.400/60.96	NO	
-Y24	1 X 24	2.300/58.42	2.617/66.47	2.500/63.50	NO	
-Y25	1 X 25	2.400/60.96	2.717/69.01	2.600/66.04	NO	
-Y26 THRU -Y50					NO	
-Y07P	1 X 7	.600/15.24	.917/23.29	.800/20.32	YES	
-Y08P	1 X 8	0.700/17.78	1.017/25.83	0.900/22.86	YES	
-Y09P	1 X 9	.800/20.32	1.117/28.37	1.000/25.40	YES	
68617-Y12P	1 X 12	1.100/27.94	1.417/35.99	1.300/33.02	YES	

OBSOLETE
NOTE 10 & 11
NOTE 10 & 11

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family DUBOX			
ltr				ecn		no		dr		date		title	
X												SMT SINGLE ROW LATCHED VCC ASSEMBLY	
												dwg no	
												sheet 5 of 5 size	
												68617 A3	
												type Product Customer Drawing	
sheet index				revision sheet									

form: A3