



Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFSplit Bolt, ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'SBC500-1'

Your search criteria matched only one product, shown below

SBC500-1



- For Use with Copper Code Conductors
- Made from high strength copper alloy to resist corrosion and provide premium electrical and mechanical performance
 - Offered with extra long body to allow connection of one or two taps to a single run conductor
 - Wide wire range -taking capability minimizes inventory requirements
 - Nut hex provides correct fit with socket, box, or open end wrenches resulting in proper torquing of electrical connection
 - Pressure bar provides secure connection on a full range of conductor combinations used with each connector assuring premium wire pull -out strength
 - UL Listed and CSA Certified for use up to 600 V and temperature rated 90°C

	Part Number	SBC500-1
	RoHS Compliancy Status	Compliant
	Part Description	Copper split bolt connector, type SBC.
	Product Type	Mechanical Connectors- Split Bolt
	CSA Certified	Yes
	UL Listed	Yes
	Length (In.)	2.83
	Length (mm)	74.4
	Min. Tap with One Max. Run	2/0 STR
	Range of Equal Run & Tap Min.	300 kcmil
	Range of Equal Run and Tap Max.	500 kcmil
	Body Hex	1.33
	Inside Diameter (In.)	.81
	Nut Hex	1.74
	Pricing Description	Split Bolt, Copper, 300- 500 kcmil
	Tightening Torque (InLbs)	825
	Tightening Torque (Nm)	(93.2)
	Wire Range (mm ²)	10 – 240
	Min. Order UOM	PC
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.