

MNX ABS 125/125 HG



Sample photo

Order symbol: ABS 125/125 HG
Product nbr: 6081310
Description: Enclosure, ABS
Remarks: Grey cover

EAN:	6418074022882
El. number:	
Finland:	3420535
Denmark:	8212023217
Italy:	7361065
Sweden:	2535736
Norway:	

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	130	125	Ingress Protection (EN 60529): IP 66/67
inch:		5.1	5.1	4.9	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Polyamide			NEMA Class: NEMA 1, 4, 4X, 6
Cover screws colour:		Grey			Certificates:
Gasket material:		TPE			Fimko
Temperatures:					Europe EN 62208: 2003
Short term:		-40 ... 80 °C			Gost R
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 125		Mounting plate (Galvanized steel)			
MIN 10		DIN-15 Mounting rail			
MIV 10		DIN-35 Mounting rail			
FP A 125/130		Front plate (Aluminium)			
HFP 130		Front plate hinge series (2 pcs)			
FP 22046		Wall fastening lug (4 pcs)			

