

6.02136.50 BS 18 Li

18 Volt Cordless Drill/Screwdriver BS 18

- Variospeed (V) electronics for infinitely variable speed change
- 20-level adjustable torque, plus drilling level
- Motor with high output and compact size
- Clockwise and anticlockwise rotation
- Quick stop for rapid fastening of screws
- Quick-action keyless chuck and spindle stop gear for convenient one-hand tool change: Metabo "Quick"
- Fatigue-free operation due to perfect ergonomy
- Rubber-coated handle provides a comfortable non-slip grip for the user
- High service life due to 3-level planetary metal gears
- Individual cell monitoring prevents over-discharging the battery pack
- Electronic overload protection with integrated temperature monitoring protects both the machine and the battery pack
- AIR COOLED technology for speedy charging and long service life
- Robust battery packs with capacity display for checking the charge status

Comparative technical values

Type of battery pack	Li-Ion
Battery pack voltage	18 V
Capacity of battery pack	1,3 Ah
Max. torque, soft	24 Nm
Max. torque, hard	48 Nm
Drill diameter in	
- Steel	10 mm/5 mm
- Wood	20 mm/16 mm
No-load speeds	0 - 450 / 0 - 1.650 /min
Drill spindle thread	1/2" -20 UNF
Chuck capacity	1 - 10 mm
Weight (including battery pack)	1,4 kg

Scope of delivery

2 Li-Power Compact battery packs (18 V/1.3 Ah), AIR COOLED quick charger ASC 30