


COBAGRiP Light



- Ideal solution for slip hazards such as split liquid or ice.
- Available in a range of colours to meet all DDA requirements.
- Suitable for use with forklift traffic.
- Simply bond or screw to the existing floor surface.

Product height: 3mm GRP base overall 5mm.

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Surface	Colour	Part Code
1.2 x 1.2	2.30 Kg/ sqm						Black	GRP010002L
							Grey	GRP060002L
1.2 x 2.4							Black	GRP010001L
							Grey	GRP060001L

Chemical Resistance Guide:

Chemical	Max .Operation Temp (°C)	
	Concentration (%)	Iso
Acetic Acid	50	125/52
Aluminium Hydroxide	100	160/71
Ammonium Chloride	ALL	170/77
Ammonium Bicarbonate	15	125/52
Ammonium Hydroxide	28	N/R
Ammonium Sulfate	ALL	170/77
Benzene	ALL	N/R
Benzoic Acid	SAT	150/66
Borax	SAT	170/77
Calcium Carbonate	ALL	170/77
Calcium Nitrate	ALL	180/82
Carbon Tetrachloride	1000	N/R
Chlorine Water	SAT	80/27

Citric Acid	ALL	170/77
Copper Chloride	ALL	170/77
Copper Cyanide	ALL	170/77
Copper Nitrate	ALL	170/77
Ferric Chlorid	ALL	170/77
Ferrous Chloride	ALL	170/77
Formaldehyde	50	75/24
Gasoline	100	80/27
Glucose	100	170/77
Glycerin	100	150/66
Lithium Chloride	SAT	150/66
Magnesium Chloride	ALL	170/77
Magnesium Nitrate	ALL	140/60
Magnesium Sulfate	ALL	170/77
Mercuric Chloride	100	150/66
Mercurous Chloride	ALL	140/50
Nickle Chloride	ALL	170/77
Nickle Sulfate	ALL	170/77
Nitric Acid	20	70/21
Oxalic Acid	ALL	75/24
Potassium Chloride	ALL	170/77
Potassium Dichromate	ALL	170/77
Potassium Nitrate	ALL	170/77
Potassium Sulfate	ALL	170/77
Propylene Glycol	ALL	170/77
Sodium Cyanide	ALL	170/77
Sodium Nitrate	ALL	170/77
Sodium Chloride	ALL	160/71
Vinegar	100	170/77
Zinc Nitrate	ALL	170/77

End of document