

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
		REVISED PER ECO-10-013614		13OCT10	HMR	CR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN OVER COPPER ALLOY.
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE. (EXCEPT WHERE NOTED.)
PITCH (TERMINAL SPACING): .375"

ELECTRICAL:
RATED CURRENT UL/CSA:
CLASS C: 20A, 300V
CLASS D: 5A, 600V
WIRE RANGE: 12-22 AWG

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB
OPERATING TEMP.: 105°C MAX



9.000	9.314	23	JC6-T308-23	4-1546701-2
8.625	8.939	22	JC6-T308-22	4-1546701-1
8.250	8.564	21	JC6-T308-21	4-1546701-0
7.875	8.189	20	JC6-T308-20	3-1546701-9
7.500	7.814	19	JC6-T308-19	3-1546701-8
7.125	7.439	18	JC6-T308-18	3-1546701-7
6.750	7.064	17	JC6-T308-17	3-1546701-6
6.375	6.689	16	JC6-T308-16	3-1546701-5
6.000	6.314	15	JC6-T308-15	3-1546701-4
5.625	5.939	14	JC6-T308-14	3-1546701-3
5.250	5.564	13	JC6-T308-13	3-1546701-2
4.875	5.189	12	JC6-T308-12	3-1546701-1
4.500	4.814	11	JC6-T308-11	3-1546701-0
4.125	4.439	10	JC6-T308-10	1437666-6
3.750	4.064	9	JC6-T308-09	1437666-5
3.375	3.689	8	JC6-T308-08	1437666-4
3.000	3.314	7	JC6-T308-07	2-1546701-9
2.625	2.939	6	JC6-T308-06	1437666-3
2.250	2.564	5	JC6-T308-05	1437666-2
1.875	2.189	4	JC6-T308-04	1437666-1
1.500	1.814	3	JC6-T308-03	9-1437665-9
1.125	1.439	2	JC6-T308-02	9-1437665-8
DIM. L	DIM. A	NO. OF POS.	CATALOG NUMBER	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .010
4 PLC ± -
ANGLES ± -
FINISH -

DWN S SCHLEGEL 1/25/06
CHK S YODER 1/25/06
APVD S YODER 1/25/06

PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME JC6-T308-XX ASSEMBLY

SIZE A3 CAGE CODE 00779 DRAWING NO C-9-1437665-8 RESTRICTED TO -

SCALE NTS SHEET 1 OF 1 REV B