

Search Results

Evaluate

- FAQ's

Design a Solution

- Specification Sheets

- PDF-24x4 FiberRu ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Install & Maintain

- Installation Instructions

- PDF-FiberRunner ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'FRIV4524X4OR'**

Your search criteria matched only one product, shown below

FRIV4524X4OR



The complete selection of fittings feature bend radius control to prevent excessive bends in high performance copper and fiber optic cabling.

- Minimum 3" (76.2mm) bend radius control fittings
- Protect against signal loss and performance degradation
- Assemble using FRBC QuikLock™ couplers
- For other standard colors replace suffix YL (Yellow) with OR (Orange) or BL (Black)

▪ Part Number	FRIV4524X4OR
▪ RoHS Compliancy Status	Compliant
▪ Product Name	24x4 Inside Vertical 45° Fitting and Cover
▪ Part Description	Attaches to 24x4 channel and/or fittings to create a 45° upward angle from a straight horizontal run. Used with outside vertical 45° angle fitting FROV4524X4OR to change level of a straight horizontal run. Includes cover.
▪ Material	ABS
▪ Color	Orange
▪ Fitting Type	Inside Vertical 45°
▪ Couplers Required	(2 pcs.) FRBC24X4OR
▪ System Type	24 x 4 FiberRunner Fitting
▪ System Size	24x4
▪ CE Compliant	No
▪ Pricing Description	Fitting and Cover, Inside Vertical 45°, 24x 4 (600mm x 100mm) FiberRunner, OR
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.