

Picosoft DG

DESCRIPTION

- Industrial protective glove.
- Knitted glove with dots on the palm and coating on the finger tips.
- 6 sizes available : 6, 7, 8, 9,10 and 11.

CHARACTERISTICS

- Seamless polyamide liner, gauge 13.
- PVC dots on the palm for extra grip performances.
- Fine and stretchable stitches for excellent comfort.
- Polyurethane coating on finger tips.
- Latex knit wrist to ensure snug fit.

PERFORMANCES

- High degree of flexibility with optimum dexterity.
- Finger tips allow very precise and safe handling.
- In compliance with the standards EN420 (General requirements) and EN388 (Mechanical Hazards) by the notified laboratory CTC, Centre Technique Cuir Chaussure et Maroquinerie, Lyon.

APPLICATIONS

- For light assembly, electronics industry, quality control and product inspection.

LIMITATIONS

- Do not use for handling liquids or pointed objects.
- Limited protection at the wrist.



This glove is certified to comply with the essential requirements of European Directive EEC/89/686 of December 21st, 1989 relative to personal protective equipment submitted to CE type examination issued by a notified laboratory, who certifies the conformity of this glove with the EN standards to which it responds and certifies the performance levels obtained during tests.



EN 420

EN 420

5 Dexterity

EN 388

0 Abrasion

1 Cut

2 Tear

1 Puncture



0121

EN 388

Mechanical hazards

			Order codes			
Sizes	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (XXL)
Picosoft DG	2F8DE06900	2F8DE01900	2F8DE02900	2F8DE03900	2F8DE04900	2F8DE00900



COMASEC

