


Item no.: 750-653/003-000
Product description: SERIAL INTERFACE RS 485 / CONFIGURABLE



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	15 (I/O System)
Transmission channel	1 Tx/D / 1 Rx/D, full duplex
Bit transfer	ISO 8482 / DIN 66259 - 4
CURRENT CONSUMPTION (INTERNAL)	65 mA
Voltage supply	via system voltage DC / DC
Isolation	500 V system / supply
Data size	1 x 24 Bit in / out (3 Bytes user data) 1 x 8 Bit Control / status
Operating temperature	0 °C ... + 55 °C
Storage temperature	-25 °C ... +85 °C
Relative air humidity	95 %
Vibration resistance	acc. IEC 60068-2-6
Shock resistance	acc. IEC 60068-2-27
Degree of protection	IP 20
EMC marine applications - noise proof	gem. Germanischer Lloyd (2003)
EMC marine applications - noise transmission	gem. Germanischer Lloyd (2003)
Conformity marking	CE
Approvals	ATEX
Cross section [mm²]	0.08 - 2.5 mm²
Cross section [AWG]	28 - 14 AWG

Connection method

Weight

Color

CAGE CLAMP® CONNECTION

48.6 g

light gray



Height	64 mm
Height	2.52 in
Width	12 mm
Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
750-653/003-000	DNV	A-12306			
750-653/003-000	GL	26 898 - 05 HH			
750-653/003-000	IECEX	IECEX PTB 07.0064X			
750-653/003-000	KR	HMB05880-AC004			
750-653/003-000	LR	02/20026 (E2)			
750-653/003-000	NK	TA06190M			
750-653/003-000	PRS	TE/1720/880590/08			
750-653/003-000	UL	E175199 Sec.1			
750-653/003-000	UL	E198726 Sec.1			
750-653/003-000	UL DEMKO A/S	08 ATEX 142851 X			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected