





REV.	DATE	DESCRIPTION
NC	11/13/01	INITIAL RELEASE



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS		DATE	TITLE			
1 HOUSING	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DO NOT SCALE DRAWING	DRAWN	G.R.S.	11/13/01	MCX STRAIGHT CRIMP PLUG (FOR RG-179/u CABLE)			
2 BODY	BER. COPPER	GOLD			CHECKED						
3 INSULATOR	TEFLON	NATURAL			ISSUED						
4 CONTACT PIN	BRASS	GOLD 30 MN.									
5 FERRULE	COPPER	GOLD									
6								SIZE	FSCM NO.	DWG. NO.	REV.
7								A	99001	252103-75.DWG	NC
8								SCALE	NA	PART NO	SHEET
									252103-75		1 OF 1

