





LEAD FINISH: SOLDER	
EYELET FINISH: SOLDER	
CAPACITANCE	22nF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	125°C 70 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
10	35
100	70
1 GHz	70
10 GHz	70



MARKING:

PART: NONE

BAG: SCI 1233-000


DATE CODE

LOT#

QTY/BAG (200 MAX.)

NOTES:

1. MAXIMUM INSTALLATION TEMP.: 500°F

	8	7	6	5	4	3	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	Description
	CN 206407	CN 202456	CN 201252	CN 194780	CN 194319	CN 170029	CHANGE NOTICE	Fractions $\pm 1/64$	Dwn. KEVERLINE	1233-000
								Dec. .xx $\pm$	Ckd. 3/21/02	
								Dec. .xxx $\pm .010$	Apvd.	
								Angles $\pm 0^{\circ} 30'$	Scale NONE	
								CODE IDENT. NO. DLSP2		

ERIE, FAIRVIEW
PENNSYLVANIA

Pi SOLDER-IN FILTER