


Restricted to: General Release

USED ON




Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: SM

Housing Color: Orange

Geom. Spec: 115-1215



VIEW C-C
NOT TO SCALE

Fiber Path

Fiber A - ——— - B
Fiber B - ——— - A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).
- 4 IL and RL tested at 1310nm.

Right Side

Connector(s): SC-Duplex

Mode: SM


Housing Color: Blue

Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS THE PROPERTY OF TYCO ELECTRONICS, INC. AND IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	B	Rev Per EC#	06-021324	9/13/2006	-	MK			
P	LTR	REVISION	RECORD	DATE	DN	APVD			



Customer Print

DRN	Cable Assy Configurator	MATERIAL	HEAT TREAT
CHK	Michael Kepko		
APVD	Michael Kepko		
NAME	FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex		
SCALE	NTS	SIZE	A2
DRAWING NO	C- 6828245	SHEET	1 of 3
REV	B		

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	MT-RJ SECURE (No Pins), Orange		SC-Duplex, Blue	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6828245-1	0.950 - 1.050	3.11 - 3.44	0.5	26	0.5	55
0-6828245-2	1.950 - 2.050	6.39 - 6.72	0.5	26	0.5	55
0-6828245-3	2.950 - 3.050	9.67 - 10.00	0.5	26	0.5	55
0-6828245-4	3.920 - 4.080	12.86 - 13.38	0.5	26	0.5	55
0-6828245-5	4.920 - 5.080	16.14 - 16.66	0.5	26	0.5	55
0-6828245-6	5.920 - 6.080	19.42 - 19.94	0.5	26	0.5	55
0-6828245-7	6.920 - 7.080	22.70 - 23.22	0.5	26	0.5	55
0-6828245-8	7.920 - 8.080	25.98 - 26.50	0.51	26	0.51	55
0-6828245-9	8.850 - 9.150	29.03 - 30.01	0.51	26	0.51	55
1-6828245-0	9.850 - 10.150	32.31 - 33.30	0.51	26	0.51	55
1-6828245-1	10.850 - 11.150	35.59 - 36.58	0.51	26	0.51	55
1-6828245-2	11.850 - 12.150	38.87 - 39.86	0.51	26	0.51	55
1-6828245-3	12.850 - 13.150	42.15 - 43.14	0.51	26	0.51	55
1-6828245-4	13.850 - 14.150	45.43 - 46.42	0.51	26	0.51	55
1-6828245-5	14.850 - 15.150	48.72 - 49.70	0.51	26	0.51	55
1-6828245-6	15.840 - 16.160	51.96 - 53.01	0.51	26	0.51	55
1-6828245-7	16.830 - 17.170	55.21 - 56.33	0.51	26	0.51	55
1-6828245-8	17.820 - 18.180	58.46 - 59.64	0.51	26	0.51	55
1-6828245-9	18.810 - 19.190	61.71 - 62.95	0.51	26	0.51	55
2-6828245-0	19.800 - 20.200	64.96 - 66.27	0.51	26	0.51	55
2-6828245-1	20.790 - 21.210	68.20 - 69.58	0.51	26	0.51	55
2-6828245-2	21.780 - 22.220	71.45 - 72.90	0.52	26	0.52	55
2-6828245-3	22.770 - 23.230	74.70 - 76.21	0.52	26	0.52	55
2-6828245-4	23.760 - 24.240	77.95 - 79.52	0.52	26	0.52	55
2-6828245-5	24.750 - 25.250	81.20 - 82.84	0.52	26	0.52	55
2-6828245-6	25.740 - 26.260	84.44 - 86.15	0.52	26	0.52	55
2-6828245-7	26.730 - 27.270	87.69 - 89.46	0.52	26	0.52	55
2-6828245-8	27.720 - 28.280	90.94 - 92.78	0.52	26	0.52	55
2-6828245-9	28.710 - 29.290	94.19 - 96.09	0.52	26	0.52	55
3-6828245-0	29.700 - 30.300	97.44 - 99.40	0.52	26	0.52	55
3-6828245-1	30.690 - 31.310	100.68 - 102.72	0.52	26	0.52	55
3-6828245-2	31.680 - 32.320	103.93 - 106.03	0.52	26	0.52	55
3-6828245-3	32.670 - 33.330	107.18 - 109.35	0.52	26	0.52	55
3-6828245-4	33.660 - 34.340	110.43 - 112.66	0.52	26	0.52	55
3-6828245-5	34.650 - 35.350	113.68 - 115.97	0.52	26	0.52	55
3-6828245-6	35.640 - 36.360	116.92 - 119.29	0.53	26	0.53	55
3-6828245-7	36.630 - 37.370	120.17 - 122.60	0.53	26	0.53	55
3-6828245-8	37.620 - 38.380	123.42 - 125.91	0.53	26	0.53	55
3-6828245-9	38.610 - 39.390	126.67 - 129.23	0.53	26	0.53	55
4-6828245-0	39.600 - 40.400	129.92 - 132.54	0.53	26	0.53	55
5-6828245-0	49.500 - 50.500	162.40 - 165.68	0.54	26	0.54	55

Qty	U of M	Description	Item No.
1	piece	DUST COVER, MT-RJ	1
1	piece	SPRING, MT-RJ, 3.8 DESIGN	2
1	piece	PIN KEEPER, 3.8MM	3
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	4
1	piece	CRIMP EYELET, MT-RJ	5
1	piece	MT-RJ Keyed Connector Housing - Orange	6
2	piece	LC, SC, FC Straight Boot, Blue	7
1	piece	MT-RJ FERRULE, THERMOPLAST SM	8
2	piece	SC Simplex Housing, Blue	9
2	piece	2.5mm ferrule cover	10
AR	meter	2 fiber, SM, 1.8 mm, Twinzip, Yellow, OFNR (Riser)	11
1	piece	MT-RJ TwinZip Bend Limiting Boot, Blue	12
2	piece	SC Duplex Clip	13
2	piece	Eyelet/Shrink tube assembly - Yellow	14
2	piece	CONN ASSY, SM, SC 1.6MM/125.5UM	15
2	piece	Trace Label	16

B	Rev Per EC#	06-021324	9/13/2006	-	MK		
P	LTR	REVISION RECORD	DATE	DIN	APVD		

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

DIN	Cable Assy Configurator	MATERIAL	-	HEAT TREAT	-
OK	Michael Kepko	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD	Michael Kepko				
NAME	FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex				
SCALE	SIZE	DRAWING NO	SHEET	REV	
NTS	A2	C- 6828245	2 of 3	B	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

DN Cable Assy Configurator		MATERIAL -	HEAT TREAT -
OK Michael Kepko	 AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APD Michael Kepko			
NAME FO C/A - 2 fiber, SM, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex			
SCALE NTS	SIZE A2	DRAWING NO C- 6828245	SHEET 3 of 3
			REV B