



SHOULDER ELECTRONICS LIMITED

BANDPASS FILTER

Type	Center Frequency (MHz)	Insertion Loss	Passband Width		Spurious Response(dB)		Package	Overseas Type
			$\pm$ 3dB	$\pm$ 30dB	Lower	Upper		
BF36A2D	36.00	21 $\pm$ 2	8.1	9.4	32	32	SIP5D	X6857D
BF43A2D	43.75	15 $\pm$ 2	6	7.6	35	35	SIP5D	X6864D
BF43A1D	43.75	15.2 $\pm$ 2	6.2	7.6	35	35	SIP5D	X6964D
BF44A2D	44.00	15.1 $\pm$ 2	6.2	7.6	35	38	SIP5D	X6866D
BF23A1D	23.40	11.8 $\pm$ 2	1.8	3.1	33	36	SIP5D	X6863D
BF36A1M	36.125	20.3 $\pm$ 2	8	9.4	30	30	SIP5K	X6966M
BF43A1M	43.75	15 $\pm$ 2	6	7.6	35	35	SIP5K	X6964M
BF44A1M	44.00	14.7 $\pm$ 1.5	6	7.6	35	35	SIP5K	X6965M
BF44A2M	44.00	15 $\pm$ 2	1.7	2.9	35	32	SIP5K	X6959M
BF46A1M	46.59	14.3 $\pm$ 2	6	7.6	35	35	SIP5K	X6852M
BF49A1M	49.125	12.2 $\pm$ 2	0.72	1.95	34	34	SIP5K	X6921M
BF44A3M	44.00	14.5 $\pm$ 2	1.8	2.7	32	24	SIP5K	X9650M
	44.00	15.0 $\pm$ 2	1.2	2.4	32	25		
BF389A1M	38.912	18.7 $\pm$ 2	1.52	2.62	36	38	SIP5K	X6922M

[SAMPLE](#)
[DIMENSIONS](#)
[TEST CIRCUIT](#)

ii



[[Home](#) | [About SDE](#) | [Request Info](#) | [Saw Filter](#) | [Saw Resonator](#) | [Ceramic Resonator](#) | [Ceramic Discriminator](#) | [Ceramic Filter1](#) | [Ceramic Filter2](#) | [Ceramic Trap](#) | [Crystal Unit](#) | [Clock Oscillator](#) | [Dielectric Filter](#) | [Dielectric Resonator](#)]

Copyright 2001 by Shoulder Electronics Limited
 Contact Us: Tel: 86-755-2979884 Fax:86-755-2979885
 Questions or comments: info@china-shoulder.com