

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

94030-4030

Status:

Active

Overview:

Quick-Disconnect Terminals

Description:

Quick Disconnect, Female, for (1.00-2.50mm²) 14-16 AWG Wire, Accepts 4.75 x 0.81mm Tab




image - Reference only

Series

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Quick Disconnects
Series	94030
Crimp Quality Equipment	Yes
Insulated	No
Overview	Quick-Disconnect Terminals
Product Name	N/A
Type	Quick Disconnect
UPC	800754325400

Physical

Barrel Type	Open
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Unplated
Net Weight	0.402/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	4.75mm
Temperature Range - Operating	80°C
Wire Insulation Diameter	2.70-4.30mm
Wire Size AWG	14, 16
Wire Size mm²	1.00-2.50

Electrical

Voltage - Maximum	250V
-------------------	------

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-94030-403
---------------	--------------

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

94030Series

Use With

94095-6030 , 94095-6040

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION