


Brand-Rex

Brand-Rex Part Number

Rev

www.brand-rex.com

RG 179 PE with Silver Plated Copper Covered Steel Conductor



PHYSICAL CHARACTERISTICS

- Inner Conductor: 30 AWG, 7/0.102 mm Silver Plated Copper Covered Steel, 0.31 mm Nom Diameter
 Diameter: Min 0.28 mm
 Max 0.33 mm
- Dielectric: Extruded solid Low Density Polyethylene Natural.
 Diameter: Min 1.63 mm
 Max 1.70 mm
- Outer Conductor: Single Braid of 38 AWG, 0.102 mm Tin Plated Copper Wire, 90% Min Coverage.
 Diameter: Max 2.13 mm
- Jacket: Extruded PVC Black.
 Diameter: Min 2.41 mm
 Max 2.67 mm
- Print Legend: To be decided

ELECTRICAL CHARACTERISTICS

- Impedance: 75 Ohms Nom
 Attenuation: 69 dB/100 m at 400 MHz
 Capacitance: 68.8 pF/m Nom
 Conductor DCR: 802 Ohm/km Max at 20°C

GENERAL INFORMATION

- Operating Temperature Range: 0°C to +70°C
 Weight: 11.5 kg/km Nom
 Rohs Compliance: Yes

Datasheet No.		L6455		© Brand-Rex Limited		Additional Details				
Rev	Date	Initials	Amendment			DFE 6415				
1	3/5/07	DJ	Initial Issue							
						Action	Name	Date		
						Issued By	D. Jukes.	3/5/07		
						Reviewed By	M. Chorlton.	3/5/07		
Headquarters and Registered Offices										
Viewfield Industrial Estate, Glenrothes, Fife. KY6 2RS, Scotland				West Bridgewater Street, Leigh, Lancashire, WN7 4HB, England						
Tel: +44 (0) 1592 772124				Fax: +44 (0) 1592 775314		Tel: +44 (0) 1942 265500			Fax: +44 (0) 1942 265576	
This drawing is the exclusive property of Brand-Rex Limited and must not be copied or reproduced in any way whatsoever without the express consent in writing of Brand-Rex Limited. The drawing is to be used only for the purpose for which it is supplied and must be returned on demand. The contents of the drawing must moreover be treated as strictly confidential and must not be disclosed to any third party without the express consent in writing of Brand-Rex Limited.										