



WT-20

Conductivity / TDS Pen-Type Water Quality Meter

Keep the costs and risks of maintaining water quality, distribution and waste under control with these easy to use, one touch water management testers. Allows facility managers to take control of monitoring regulatory compliance and troubleshoot corrosion in building water/waste water systems.

- Dual LCD display with conductivity or TDS and temperature (selectable C and F)
- Adjustable TDS factor from 0.4 to 1.0
- Waterproof and dustproof - IP65
- Convenient to use membrane keypad
- Quick response and easy to calibrate
- Auto power off
- Data hold
- Pen size, easy to fit in pocket.
- Low battery indicator
- Auto power off disable
- Easy one-touch multi point calibration

No hassle warranty

No waiting.

No shipping charges.



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)



WT-20 Conductivity / TDS Pen-Type Water Quality Meter

Data Sheet

Specifications

Conductivity	0~1999 uS / 0~19.99 mS
TDS Range	0~1999 ppm / 0~19.99 ppt
Resolution	1 uS or 0.01mS or 0.01ppt or 1ppm
Accuracy	±1% Full Scale ±1 dgt
Calibration Standard Range	(0.2~1) * full scale
Operating Temperature	0°C to 50°C (32°F to 122°F)
Temperature Compensation	0°C to 50°C (32°F to 122°F)
Temperature Coefficient	0~4.0% per degree C
Normalization Temperature	20°C or 25°C (68°F or 77°F)
Power Requirements	4x 1.5V batteries (Type A76 or LR44)
Calibration	2 point (Calibration range is ± 30% of factory default parameter)
Dimension	165 x 35 x 32mm (6.5 x 1.4 x 1.3 in)
Weight	Approx. 56g (0.12 lb)

Amprobe® Test Tools

website: www.Amprobe.com
email: info@amprobe.com
Everett, WA 98203
Tel: 877-AMPROBE

Amprobe® Test Tools Europe

In den Engematten 14
79286 Glottertal, Germany
Tel.: +49 (0) 7684 8009 - 0

©2009 Amprobe Test Tools. All rights reserved.
7/2009 3520488 Rev A