




Product Data Sheet


Part No. PB-4314 Non-Washable Type

PB-4314



Φ 42.5 × H14.0

DIMENSIONS



Type	Unit	PB-4314
Rated Voltage	(VDC)	12
Operating Voltage	(VDC)	3~28
Current Consumption	(mA)	< or = 8
Sound Output (Min)	(dB)	> or = 90
Resonance Frequency	(Hz)	2800±500
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	11
Dimension	mm	42.5 x H14
*Value applying at rated voltage		
*distance for measurement 30cm		