



BURNDY Catalog Number
UPC Number
Description
Status

KA34
 7818103658544
 4/0-500 CU LUG ST SCR 1H
 Active

Web Use
 BURNDY Product Line

Dimensional

Size (Hex) or Size (Bolt)	64/79
Length (in)	2.55
Thickness (in)	7/25
Height (in)	2.09
B Length (Fraction)	1-3/25
Hole Size (Fraction)	9/16
Stud Size (in)	1/2
Thickness	0.28
Size (Hex) or Size (Bolt) - in	0.81
B Length (in)	1.12
Pad Width (in)	1.38
N (Fraction)	9/16
N (in)	0.56
Hole Size (in)	0.56
Length (Fraction)	2-9/16
Height (Fraction) (in)	2-3/32

General

Product Description	Copper Terminal, 1 Hole, 4/0 AWG (Str)-500 kcmil, 1/2" Stud, 1 Screw
---------------------	--

Conductor(s)

Copper Solid Size (Range)	N/A
Copper Stranded (Range)	4/0 AWG-500 kcmil

Physical

Screw Type	Allen
Type of Hardware	13 /16 "
Installation Torque	375
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	N
ROHS Compatible	Exempt
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175