



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

## 10Gb Duplex Multimode 50/125 OM3 LSZH Fiber Patch Cable, (LC/LC) - Aqua, 25M (82-ft.)

MODEL NUMBER: **N820-25M**



### Description

Tripp Lite introduces its new OM3 Laser-Optimized Multimode Fiber (LOMMF) "Aqua" cables, for use with 10Gb Ethernet applications. These new technology, 50/125um, LC/LC Fiber Optic cables, provide nearly three times the bandwidth over conventional 62.5um multimode fiber, with performance rivaling that of Single mode cable, at a much reduced cost. LOMMF cable allows 10Gb serial transmission over extended distances in the 850nm wavelength window, where low-cost Vertical Cavity Surface Emitting Lasers (VCSELs) enable a cost-effective, high-bandwidth solution. LOMMF is ideally suited for LAN's, SAN's, and high-speed parallel interconnects for head-ends, central offices, and data centers.

### Features

- 25 Meter LC/LC 50/125 10Gb Aqua Fiber Patch Cable, OM3 Rated
- 10gb Ethernet speed to 300 meters @850nm
- Use with VCSEL and LED laser light sources
- High-Speed, High-Bandwidth, Low-Cost
- Backward compatible with legacy LAN's
- Ideal for Fibre Channel (SAN) applications
- IEEE 802.3ae and TIA LOMMF compliant

## Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	

### Highlights

- 25 Meter LC/LC 50/125 10Gb Aqua Fiber Patch Cable...OM3 Rated
- Designed for 10-Gig Ethernet applications
- Backward compatible with existing 50/125 fiber
- Max 10Gb distance of 300 meters @850nm
- Low-Smoke, Zero Halogen (LSZH) Aqua jacket

### Applications

- For use with 10-Gigabit Ethernet equipment

### Package Includes

- 25 meter Duplex Multimode 50/125 OM3 Aqua Fiber Patch Cable, LC/LC



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Clad Diameter	125um
Core Diameter	50um
Fiber Type	50/125 - OM3
Number of Fibers	2
Intended Application	Computer Networking (Fiber)
Cable Type	10GIG AQUA MULTIMODE 50/125 FIBER OPTIC
Model Type	LC/LC
Network Speed	10Gbps / 40Gbps / 100Gbps
<b>INPUT</b>	
Cable Length (m)	25
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332149923
<b>PHYSICAL</b>	
Color	Aqua
Style	Fiber Optic
<b>CONNECTIONS</b>	
Connector A	LC
Connector B	LC
Number of Connectors	4
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.