

Connector units

with mixed components 750 V~ Gr. c, 16A/35A with locking lever on broad side

7/33

part no. PQP

socket insert screw insert
4 contacts 35 A 6 mm²
6 contacts 16 A 2,5 mm²




72.205.1053.0

plug insert screw connection
4 contacts 35 A 6 mm²
6 contacts 16 A 2,5 mm²





72.215.1053.0

fixing distances
and openings
for open housing bottom parts




plug insert



part no. POP sizes of the cable entries

hood
with screw connection

77.350.1628.0



93.5


43

60

77.350.1628.1¹⁾
77.350.1628.2²⁾ 10 Pg 21

hood
with screw connection

77.351.1628.0



93.5

43

60

77.351.1628.1¹⁾
77.351.1628.2²⁾ 10 Pg 21

hood
with screw connection

77.352.1628.0



93.5


43

60

77.352.1628.1¹⁾
77.352.1628.2²⁾ 8 Pg 21

hood
with strain relief

77.360.1628.0



93.5

43

60

77.360.1628.0 7 Pg 21

hood
with strain relief

77.361.1628.0



93.5


43

60

77.361.1628.0 8 Pg 21

hood
with strain relief

77.362.1628.0



93.5

43

60

77.362.1628.0 8 Pg 21

special types: 1) only with Pg thread
2) intermediate supports with Pg thread