

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120985006

Status:

Active

Overview:

IP67-Rated HarshIO Modules

Description:

Brad HarshIO Digital Module for CANopen, Compact 30mm, IP67, 8 Ports M8, 8 Inputs, NPN



Documents:	
3D Model	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	Product Literature (PDF)
Drawing (PDF)	

Agency Certification	
UL	E200650
General	
Product Family	Industrial I/O Modules
Series	112098
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	CiA, UL, cUL, CE
IP Rating	IP67
Overview	IP67-Rated HarshIO Modules
Product Literature Order No	987650-9332
Product Name	HarshIO CanOpen
Protocol	CANopen
Software Downloads	TBDCO-8xxx-xxx
UPC	883906226671
Physical	
Bus Input	5-pole Micro-Change (M12), A-Coded, Male
Bus Output	5-pole Micro-Change (M12), A-Coded, Female
Format	Compact (30mm)
Housing Width	30.00mm
I/O Connector	3-pole Nano-Change (M8), Female
I/O Ports	8x M8
I/O Signal Mix	8 input
Mechanical Shock	10G, 11ms, 3 AXIS
Power Input	Via Bus Connector
Power Output	None
Temperature Range - Operating	-25°C to +70°C
Vibration	IEC 60068-2-6
Electrical	
Current - Maximum Output	N/A
EMC	IEC 61000-6-2
Input Delay	2.5ms
Input Device Supply	200 mA per port at 25°C
Input Type	NPN or Dry Contact
Material Info	
Engineering Number	TBDCO-880N-804
Reference - Drawing Numbers	
Sales Drawing	1120985001-000, TBDCO-8XXX-804

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112098 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION