


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	REV PER ECR 10-000722	22JAN10	JR	TM



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 2/0W* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0.00254 [0.000100] MIN THK
EXT. PER ASTM B-545
- 4 MAX RECOMMENDED OPERATING TEMP
IS 170°C.
- 5 WIRE CROSS SECTIONAL AREA RANGE:
60.6-76.3mm [119,500-150,500] CMA
SOLID OR STRANDED.

50	LOOSE PIECE	36921
QTY	PACKAGING TYPE	PART NO.
Tyco Electronics Corporation Harrisburg, PA 17105-3608		
NAME TERMINAL, RING TONGUE, SOLISTRAND		
SIZE	CAGE CODE	DRAWING NO
A2	00779	C=36921
RESTRICTED TO	SCALE	SHEET
-	2:1	1 of 1
REV	G	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	DK SCHRUM	1/13/94
DIMENSIONS: INCHES		CHK	AJ KAUFMAN	1/19/94
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	JL MECKLEY	1/19/94
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± 0.20[0.008]		WEIGHT	-	
3 PLC ± -		CUSTOMER DRAWING		
4 PLC ± -				
ANGLES ± -				
FINISH				