

H.K. Porter
14" Industrial Grade, Center Cut Cutter



◀◀ previous print close next ▶▶

Product Details	
Catalog No.	1490MC
UPC Code	037103913777
Weight / Length	2 3 / 4 lbs. / 14 in.
Handle Material	Tubular Steel
Jaw Design / Cutting Blade	All Purpose / Center Cut
Replacement Cutterhead / Jaws	1413C
Capacity	See Tech Specs Link Below
Material Hardness	See Tech Specs Link Below
Brinell / Rockwell	See Tech Specs Link Below
Packaging	Industrial Box / Carton
Literature	Safety- Hand Tool Selection.pdf
Tech. Spec.	1490MC Specifications.pdf
Lineart	1490MC.pdf
Low Res. Image	1490MC 100.jpg
High Res. Image	1490MC 300.jpg
Parts List	Parts for 1490MC.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

Email this Page

Product Features:

- General plant maintenance tool
- Drop-forged, precision ground, alloy tool steel jaws, center-cut blades
- Cuts soft, medium, or hard materials
- Maximum hardness of material to be cut: Brinell 455 / Rockwell C48
- Lockplate keeps jaws from loosening
- Toggle joints turn 50 lb hand pressure to 4000 lb of cutting pressure

- **Screw-type adjustment realigns edges**
- **Steel handles with rubber grips**
- **Replacement cutterhead: 1413C**
- **NEVER use any H.K. Porter cutters on energized circuits, wire, or cable!**