






POSITION LOCK 1 2 3 - - - - - N 2 N-IN



SECT.W-W(LOCK PART)




SECT.V-V(W/O LOCK PART)

注記 NOTES:

1. 使用材料 MATERIAL
ウエハー:液晶ポリマー ガラス充填 UL94V-0 (黒)
WAFER:LIQUID CRYSTAL POLYMER(GLASS FILLED)
UL94V-0 (COLOR:BLACK)
ピン:黄銅 (t=0.15)
PIN:BRASS(t=0.15)
2. メッキ仕様 PLATING
ピン PIN
金メッキ 0.25マイクロメートル以上 (コンタクト部)
GOLD 0.25MICROMETER MINIMUM (CONTACT AREA)
金メッキ 0.4 マイクロメートル以下 (テール部)
GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)
下地メッキ:ニッケルメッキ1.5 マイクロメートル以上
UNDER PLATING : NICKEL 1.5MICROMETER MINIMUM
3. (全極数/2) = 偶数の場合に適用。
APPLY FOR (CIRCUIT/2)=EVEN.
4. 嵌合相手:54796 シリーズ
MATE WITH : 54796 SERIES
5. テール平坦度は、0.08以下
TAIL COPLANARITY TO BE 0.08MAXIMUM

NONE	18.54	17.6	19.49	55622-0901	90
	16.54	15.6	17.49	55622-0801	80
6,8,10,12,23,25	12.54	11.6	13.49	55622-0601	60
6,7,8,9,10,16,17,18,19,20	10.54	9.6	11.49	55622-0501	50
2,4,6,7,8,9,10,11,12,13,14,15,17,19	8.54	7.6	9.49	55622-0401	40
ALL	6.94	6.0	7.89	55622-0321	32
LOCK POSITION	C	B	A	MATERIAL NO.	Ck+

REVISED EC NO: J2005-3837 DRAWN: NESUZUKI CHKD: KATOJO APPR: NUKITA REV T	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	MODEL NO. 55622-***1	THIRD ANGLE PROJECTION	
		10 UNDER	±0.2	DRAWN BY SAI HARA	DATE 00/05/30	TITLE 0.4 B-TO-B PLUG ASSY WITHOUT NAIL (HGT=1.5) -LEAD FREE-				
		10 OVER 30 UNDER	±0.25	CHECKED BY TITO	DATE 02/12/17					
		30 OVER	±0.3	APPROVED BY TOYAMAGUCHI	DATE 02/12/17	MOLEX INCORPORATED				
		ANGULAR	±3 °	MATERIAL NO.	DOCUMENT NO.					
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-55622-003		SHEET NO. 1 OF 2		
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								



嵌合断面図 (参考)
MATED DRAWING (REFERENCE)

参考基板レイアウト (マウント面)
P.C. BOARD PATTERN DIMENSION. (REFERENCE)
(MOUNTING AREA)

REVISED EC NO: J2005-3837 DRAWN:SUZUKI CHK:KATOJO APP:NUKITA		DESCRIPTION 2005/06/23 2005/06/24 2005/06/30	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	MODEL NO. 55622-***I	
						MM ONLY		---	METRIC	THIRD ANGLE PROJECTION	
				10 UNDER ±0.2		DRAWN BY DATE	TITLE 0.4 B-TO-B PLUG ASSY WITHOUT NAIL (HGT=1.5) -LEAD FREE-				
				10 OVER 30 UNDER ±0.25		CHECKED BY DATE					
				30 OVER ±0.3		APPROVED BY DATE					
				ANGULAR ±3 °		TOYAMAGUCHI 02/12/17	MOLEX MOLEX INCORPORATED				
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
SEE CHART		SD-55622-003				2 OF 2					
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

DWG. NO.
SD-55622-004

F

D

C



B

DO NOT SCALE DRAWING

8 7 6 5 4 3 2 1

引き出し方向
PULL OUT
DIRECTION

REEL




DETAIL "F"

NOTES


- 製品詳細寸法については図面 SD-55622-003 を参照下さい。
RE DETAILED DIMENSION, SEE SD-55622-003
- 梱包数量：3000個/リール
NUMBER OF CONNECTORS : 3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH
20PCS.MIN. トップテープ接着部 (空エンボス)

引き出し方向
PULL OUT
DIRECTION



- トップテープの剥離強度：0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE : 0.1N ～ 0.7N(10.2gf ～ 71.4gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED , DURING TRANSPORTATION.

引き出し方向
PULL OUT
DIRECTION



- 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOPTAPE)：PET、PE、PEF
リール(REEL)：ポリスチレン(PS) <リサイクル材を含む>
POLYSTYRENE(PS) <RECYCLE MATERIAL CONTAINED>

無鉛
LEAD FREE

E04NO. DRWN: CHK: APPR:		E03NO. DRWN: CHK: APPR:		E02NO. DRWN: CHK: APPR:		REVISED '02/12/17 E01NO. J2003-1681 DRWN: R.TAKEUCHI CHK: T.IITO APPR: TO.YAMAGUCHI		REVISED '02/04/03 E00NO. J2002-2503 DRWN: T.KAIHO CHK: T.IITO APPR: TO.YAMAGUCHI		DESCRIPTION		MATERIAL 材料 注記参照 SEE NOTES		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE —/—		DESIGN UNITS ☒ mm ☐ INCH		FIRST ANGLE PROJECTION		☐ mm INCH ☐ mm ONLY		REVISE ON CAD ONLY					
												FINISH 仕上り		10 UNDER 未満		±0.2		DRAWN BY & DATE S.AIHARA '00/5/30		TITLE: 0.4 B-To-B PLUG Assy W/O NAIL (Hgt=1.5) Embstp Pkg									
														10 OVER 30 UNDER 以上 未満		±0.25		CHECKED BY & DATE T.IITO '02/12/17											
														30 OVER 以上		±0.3		APPROVED BY & DATE TO.YAMAGUCHI '02/12/17		MOLEX INCORPORATED									
														WIRE RANGE 適用電線範囲				ANGLE 角度		±3°		CAD FILENAME 55622004.S01		MATERIAL NO. SEE CHART		DRAWING NO. SD-55622-004		SHEET NO. 1 OF 3	
						F		E		REV		INS. RANGE 被覆外径						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE B									

DWG. NO.
SD-55622-004

F

D

V

C

B

DO NOT SCALE DRAWING

DESIGN NO. DRAWN: CHK'g: APPR:	DESIGN NO. DRAWN: CHK'g: APPR:	DESIGN NO. DRAWN: CHK'g: APPR:	REVISED '02/12/17 DESIGN NO. J2003-1681 DRAWN: R.TAKEUCHI CHK'g: T.ITO APPR: TO.YAMAGUCHI	REVISED '02/04/03 DESIGN NO. J2002-2503 DRAWN: T.KAIHO CHK'g: T.ITO APPR: TO.YAMAGUCHI	DESCRIPTION REV
			F	L	

MATERIAL 材料	注記参照 SEE NOTES
FINISH 仕上げ	
WIRE RANGE 適用配線範囲	
INS. RANGE 被覆外径	


GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE —//—
10 UNDER 未満	±0.2
10 OVER 30 UNDER 以上 未満	±0.25
30 OVER 以上	±0.3
ANGLE 角度	±3°

MODEL NO. DESIGN UNITS mm INCH	DESIGNED BY & DATE S.AIHARA '00/5/30
55622-***8	CHECKED BY & DATE T.ITO '02/12/17
APPROVED BY & DATE TO.YAMAGUCHI '02/12/17	CAD FILENAME 55622004.S02

TITLE: 0.4 B-To-B PLUG Assy W/O NAIL (Hgt=1.5) Embstp Pkg	
MOLEX INCORPORATED	
MATERIAL NO. SEE CHART	DRAWING NO. SD-55622-004
SHEET NO. 3 OF 3	

32	33.5	19.69	55622-0908	90
		17.69	55622-0808	80
キャリアテープ幅 CARRIER TAPE WIDTH	B	(A)	MATERIAL NO.	極数 Ckt+

無鉛
LEAD FREE



32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE

DWG. NO.
SD-55622-004

F

D

V

C

B

DO NOT SCALE DRAWING

DESIGN NO. DRAWN: CHK'G: APPR:	DESIGN NO. DRAWN: CHK'G: APPR:	DESIGN NO. DRAWN: CHK'G: APPR:	DESIGN NO. DRAWN: CHK'G: APPR:	REVISED '02/12/17 DESIGN NO. J2003-1681 DRAWN: R.TAKEUCHI CHK'G: T.ITO APPR: TO.YAMAGUCHI
				F




MATERIAL 材料	注記参照 SEE NOTES
FINISH 仕上げ	
WIRE RANGE 適用電線範囲	
INS. RANGE 被覆外径	

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE	DESIGN UNITS ☒ mm ☐ INCH
10 UNDER 未満	±0.2	DRAWN BY & DATE S.AIHARA '00/9/25 CHECKED BY & DATE T.ITO '02/12/17 APPROVED BY & DATE TO.YAMAGUCHI '02/12/17 CAD FILENAME 55622004.S03
10 OVER 30 UNDER 以上 未満	±0.25	
30 OVER 以上	±0.3	
ANGLE 角度	±3°	

MODEL NO. 55622-***8	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	SHT 2	REV 3
-------------------------	--	----------	----------

TITLE: 0.4 B-To-B PLUG Assy W/O NAIL (Hgt=1.5) Embstp Pkg			
MOLEX INCORPORATED			
MATERIAL NO. SEE CHART	DRAWING NO. SD-55622-004	SHEET NO. 2 OF 3	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			
SIZE B			

引き出し方向
PULL OUT DIRECTION



24mm幅キャリアテープ
24mm WIDTH CARRIER TAPE

無鉛
LEAD FREE

24	25.5	13.69	55622-0608	60
		11.69	55622-0508	50
		9.69	55622-0408	40
		8.09	55622-0328	32
キャリアテープ幅 CARRIER TAPE WIDTH	B	(A)	MATERIAL NO.	極数 Ck+