


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				G	REV PER 0G3A-0363-01	10JUL01	JR/TM



AMP
WIRE RANGE

8 AWG
STRANDED

METRIC

DIMENSIONS LISTED IN mm [INCHES]

- NOTE:
- 1 STAMP AMP 8* LOCATE APPROX AS SHOWN
 2. TONGUE MATERIAL THK 1.02±0.08 [.040±.003]
 3. WIRE INSULATION DIA 9.65 [.380] MAX
 4. TAPE ITEMS ARE ON 30.48 [1.200] CENTERS

50	LOOSE PC, BOX	8-53978-2
500	ON TAPE	53978-2
100	LOOSE PC	53978-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 150°C			QTY	PACKAGE TYPE	PART NO
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600 V MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± -	DR 10-7-93 S.S. GOULDEN	AMP AMP Incorporated Harrisburg, PA 17105-3608		
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 6.64-10.54mm² [13,100-20,800] STRANDED	MATERIAL COPPER PER ASTM B-152 PVF², COLOR:NATURAL	CHK 10-7-93 R. HERSEY			
NAME								
				APPD 10-7-93 B. BARE	TERMINAL, RING TONGUE, PVF², PLASTI-GRIP, WIRE SIZE:8 AWG			
				APPD 10-7-93 M. ELLIS	PRODUCT SPEC NOT AVAILABLE	SIZE	CAGE CODE	DRAWING NO
				FINISH	APPLICATION SPEC NOT AVAILABLE	B	00779	C-53978
				TIN/LEAD (93-7) PLATE PER ASTM B545	WEIGHT -	SCALE	NTS	SHEET 1 OF 1
			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.					