


0600 Toggle Switches 1A 250Vac



C0600HD ---



C0600CC ---

- ▶ Toggle switch
- ▶ Brass and nylon actuators
- ▶ Single pole
- ▶ Latching and momentary action
- ▶ Choice of actuator profiles



C0602SC ---

Approvals and specifications

In house test: 1A 250Vac — Indicative rating only
3A 12/24Vdc — Indicative rating only


3mm contact gap.
Technical data on pages 4 & 5.

C 0600 H D ---
TERMINAL FUNCTION ACTUATOR BODY OPTIONS

▶ TERMINAL	▶ FUNCTION	▶ ACTUATOR	▶ BODY	▶ OPTIONS
C 6.3 x 0.8 10.1	0600 ON - OFF 0602 ON - OFF (momentary ON)	C Chromed brass (0600) 15.0 U Nylon (0600) 12.1 G Nylon (0600) 27.0 H Nylon (0600) 17.0 S Chromed brass stem/nylon paddle (0602 only) 41.8	D Nylon neck and top plate (Used with actuator codes U, G and H) C Metal neck and top plate (Used with actuator codes C and S) Ø12.7 1.3 11.1 Panel thickness - 3.5mm Back nut must be fitted Fixing nuts (Standard is M506 & T92) T5 Hex brass M506 Hex nylon 15.2 3.0 (M506) 2.0 (T5) T92 Knurled brass - slotted 16.0 2.6 M279 Knurled nylon 16.2 4.1	Cover A0331M0AAA (C Actuator only) Neck Seal A0539M0AAA (C, H & U Actuators) Actuator visible Cover A1080M0AAA (C Actuator only) Covers have internal nylon nuts.

Dimensions (mm)

0600 (U actuator shown)



0602

