








Miniature Combinable Right Angle for Backlighting

1.8mm LED Circuit Board Indicator

Right Angle Indicator LEDs



Part Number	LED Color	Lens Type/Color	Electrical-Optical Characteristics (Ta = 25°C)				Full Viewing Angle
			I _f = mA typ	I _v mcd typ	V _f = V typ/max	λ _p nm	
12PCT070TR4	RED	DIFFUSED	10	12.5	2.0/2.6	625	 40°
12PCT070TY4	YELLOW	DIFFUSED	10	5.5	2.1/2.6	590	
12PCT070TG4	GREEN	DIFFUSED	10	5.5	2.2/2.6	565	
12PCT070TWRG4	RED	MILKY	10	4.0	2.0/2.6	635	
	GREEN	WHITE	10	4.0	2.2/2.6	568	
12PCT070TWYG4	YELLOW	MILKY	10	2.4	2.1/2.6	585	
	GREEN	WHITE	10	4.0	2.2/2.6	568	

Part Number	LED Color	Lens Type/Color	Electrical-Optical Characteristics (Ta = 25°C)				Full Viewing Angle
			I _f = mA typ	I _v mcd typ	V _f = V typ/max	λ _p nm	
13PCT070TR4	RED	DIFFUSED	10	12.5	2.0/2.6	625	 40°
13PCT070TY4	YELLOW	DIFFUSED	10	5.5	2.1/2.6	590	
13PCT070TG4	GREEN	DIFFUSED	10	5.5	2.2/2.6	565	
13PCT070TWRG4	RED	MILKY	10	4.0	2.0/2.6	635	
	GREEN	WHITE	10	4.0	2.2/2.6	568	
13PCT070TWYG4	YELLOW	MILKY	10	2.4	2.1/2.6	585	
	GREEN	WHITE	10	4.0	2.2/2.6	568	

Part Number	LED Color	Lens Type/Color	Electrical-Optical Characteristics (Ta = 25°C)				Full Viewing Angle
			I _f = mA typ	I _v mcd typ	V _f = V typ/max	λ _p nm	
14PCT070TR4	RED	DIFFUSED	10	12.5	2.0/2.6	625	 40°
14PCT070TY4	YELLOW	DIFFUSED	10	5.5	2.1/2.6	590	
14PCT070TG4	GREEN	DIFFUSED	10	5.5	2.2/2.6	565	
14PCT070TWRG4	RED	MILKY	10	4.0	2.0/2.6	635	
	GREEN	WHITE	10	4.0	2.2/2.6	568	
14PCT070TWYG4	YELLOW	MILKY	10	2.4	2.1/2.6	585	
	GREEN	WHITE	10	4.0	2.2/2.6	568	

Part Number	LED Color	Lens Type/Color	Electrical-Optical Characteristics (Ta = 25°C)				Full Viewing Angle
			I _f = mA typ	I _v mcd typ	V _f = V typ/max	λ _p nm	
15PCT070TR4	RED	DIFFUSED	10	12.5	2.0/2.6	625	 40°
15PCT070TY4	YELLOW	DIFFUSED	10	5.5	2.1/2.6	590	
15PCT070TG4	GREEN	DIFFUSED	10	5.5	2.2/2.6	565	
15PCT070TWRG4	RED	MILKY	10	4.0	2.0/2.6	635	
	GREEN	WHITE	10	4.0	2.2/2.6	568	
15PCT070TWYG4	YELLOW	MILKY	10	2.4	2.1/2.6	585	
	GREEN	WHITE	10	4.0	2.2/2.6	568	

Part Number	LED Color	Lens Type/Color	Electrical-Optical Characteristics (Ta = 25°C)				Full Viewing Angle
			I _f = mA typ	I _v mcd typ	V _f = V typ/max	λ _p nm	
18PCT070TR4	RED	DIFFUSED	10	12.5	2.0/2.6	625	 40°
18PCT070TY4	YELLOW	DIFFUSED	10	5.5	2.1/2.6	590	
18PCT070TG4	GREEN	DIFFUSED	10	5.5	2.2/2.6	565	
18PCT070TWRG4	RED	MILKY	10	4.0	2.0/2.6	635	
	GREEN	WHITE	10	4.0	2.2/2.6	568	
18PCT070TWYG4	YELLOW	MILKY	10	2.4	2.1/2.6	585	
	GREEN	WHITE	10	4.0	2.2/2.6	568	

Bicolor LED Projection .075