


Specifications

- * Due to ongoing technological advances, consult factory for certification specifics.

The figure shows four mechanical views of connectors. The top-left view is a front elevation of the "HIGH BARRIER OPTION" connector, showing dimensions: .080[2.03] (top width), .825[20.95] (total width), .125[3.18] (top flange thickness), .677[17.20] (height to barrier), .892[22.66] (height to solder lugs), .843[21.41] (lateral offset), and .080 SOLDER LUG (labeled). The top-right view is a side elevation of the "P.C. (option 2)" connector, showing dimensions: .590[14.98] (width), .380[9.65] (flange thickness), .877[22.27] (height to top of body), and .505[12.83] (height to bottom of pins). The bottom-left view is a front elevation of the "TAB" connector, showing dimensions: .825[20.95] (width), 1.040[26.42] (height to tab), and TAB (labeled). The bottom-right view is a side elevation of the "P.C. (option 7,8)" connector, showing dimensions: .590[14.98] (width), .380[9.65] (flange thickness), .730[18.54] (height to top of body), .920[23.36] (height to top of mounting holes), and .507[12.88] (height to bottom of pins).



The diagram shows a 6-pin rocker switch with the following labels and options:

- SERIES:** 6
- ACTUATOR STYLE:** 11 PADDLE, 21 CURVED ROCKER
- BASE/ACTUATOR COLOR:**
 - BASE: 1 BLACK, 2 BLACK, 4 WHITE, 5 WHITE
 - ACTUATOR: 1 BLACK, 2 WHITE, 4 BLACK, 5 WHITE
- POLES:** 1 SINGLE POLE, 2 DOUBLE POLE, 5 DOUBLE POLE W/ HIGH BARRIERS, 6 SINGLE POLE W/ HIGH BARRIERS
- RATING:** 1 .4VA MAX @20V MAX (AC/DC), 2 2A 250VAC 5A 125VAC RESISTIVE, 3 11A 125VAC H³, 4 4A 250 VAC 8A 125VAC, 9 4A 250VAC 8A 125VAC INDUCTIVE, 6(4)A 250VAC T85⁸
- FUNCTION:** 1 ON-NONE-OFF
- TERMINATION:** 1 .080 SOLDER LUG, 2 PC TERM, 3 WIRE LEAD⁷, 4 WIRE LEAD, 6 .187 SOLDER LUG, 7 PC BACK MOUNT, 8 PC FRONT MOUNT, 9 .187TAB (QC)
- EPOXY SEALED TERMINALS:** E EPOXY, 0 NONE REQUIRED
- ROCKER FACE LEGEND:**
 - MOLDED-IN⁵: 0 NO LEGEND ON-OFF (VERTICAL), 8 I-O (HORIZONTAL), 9 I-O (VERTICAL)
 - INK TRANSFER STAMP⁶: 0 A, B, D, E, F
 - (indicates ON) (ON ROCKER RADIUS)

Rating 9 using Termination 1 or 2 is rated T55 only.

al. **N** NOT APPLICABLE
B BLACK
V VISI-RED
W WHITE