

**Description**

The backbone of any resistance soldering system is a high quality power unit. American Beauty's resistance power units are recognized industry-wide for their performance, reliability and safety. Common features include fail-safe devices to ensure ultimate user safety, flexibility to operate a variety of hand pieces, and our outstanding three-year warranty, guaranteeing the product to be free from manufacture defect and to work properly under normal operating conditions.

**Related Products**

The following products are related (similar model but different specifications, etc.) to Model 105C2 featured on this page:

Model	Product Name	
10557	Medium Duty Resistance Soldering Plumbing System	

**Replacement Products****Applications****Technical Specifications**

RoHS Compliant	Yes
Connection Type	Ring Terminals
Wattage	1800 watts
Available in 220-240VAC?	Yes
Country of Origin	US
Package Length	13.00 in / 33.02 cm
Package Width	13.00 in / 33.02 cm
Package Height	14.00 in / 35.56 cm
Shipping Weight	33.85 lbs / 15.35 kg

**User Information and Instruction Sheet**

Other Product Data Sheets

**Features and Benefits**

**1,800 Watts (7.2 VAC) of Power** with 3 unique settings provides intense power required to overcome difficult heat sinks.

Heavy-Duty Steel case protects your investment for a lifetime.

Extensively tested for **CE & RoHS compliance**, ensuring the highest level of operator health & safety.

**3/8" Stud & Wing nut** allow for firm connection of heavy-duty handpieces with ring terminal connectors.