

► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

▼ PCB connectors

■ Male headers

■ Female headers

■ Direct female connectors

■ Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

Male headers

SL 10 SMD ...

SL 10 SMD 062 7 G B SM

□ 0.635 mm, SMD-technique

... packing (option) - additions:


SL 10 SMD 040-104 ... SM; ... B SM: 4-20 contacts

SL 10 SMD 040-062 ... B TR: 4-20 contacts

SL 10 SMD 078 / 104 - 130 ... B TR: 4-12 contacts

Data sheet

add to request



Features

Technical Drawing

Equipping

Variants

Service

Accessories / related products

grid	2.54 mm
no. of contacts	7
contact material	CuSn alloy
surface of contact	gold-plated
surface contact /	Ni+≥0.2µm Au
contact sleeve	Ni+4...6µm Sn
version	male header
volume resistance	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of inflammability	UL 94 V-0
specific insulation resistance	>10.0 ⁷⁰ Ω·m
connection type	SMD
reflow solderable	yes
packing	pick and place pad and bar magazine