


HONEYWELL
PART NUMBER

141SM2-T2

PRODUCT CODE
TYS0115FAA-PMA 

REV	DOCUMENT	CHANGED BY	CHECK
11	0038113	PRS 12JUN08	BLR

.187 DIA X .125 WIDE OIL BRONZE
ROLLER (.005 T I R)



NOTES

-  - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
-  - FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 141SM2-T2 FOR FAA-PMA

RELEASE NO.
PR - 1353REPLACES
-

CHARACTERISTICS

OPERATING FORCE - - - - 7 OZ MAX

RELEASE FORCE - - - - - 2 OZ MIN

PRETRAVEL - - - - - .219 MAX

DIFFERENTIAL TRAVEL - - - .025 MAX

OVERTRAVEL - - - - - .030 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

APPROVALS

KEMA, CE

11A 250V ~ T85 1E4
5A 30 Vdc T85 1E4

UL, CSA

11A 1/4 HP 125 250 VAC
5A 30 VDCBRAND
L190

AVIATION

FAA - PMA

BRAND

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±	-
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.005
FOUR PLACE	.XXXX	±	-
ANGLES		±	-

THIRD ANGLE PROJECTION



DRAWN

VK

30 OCT 07

CHECK

RJ

30 OCT 07

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE

B

TYPE

I

DRAWING NAME

141SM2-T2

REV

11

SCALE

-

WEIGHT .008 LB MAX

SHEET 1 OF 1