




- 1

DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2

MATERIAL: HOUSING-POLYCARBONATE,CLEAR.
TERMINAL - .36 [.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μ m[.000007] THICK GOLD IN LOCALIZED PLATE AREA, OVER .762 μ m[.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μ m[.000100] THICK NICKEL ON ENTIRE CONTACT.
3.

PLUG WILL ACCEPT 26 OR 28 AWG STRANDED WIRE HAVING A MAXIMUM INSULATION DIAMETER OF 0.89-0.99[.035-.039] AND A MAXIMUM OVAL CABLE JACKET OF 2.54 X 8.89[.100 X .350].
- 4

TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- 6

10,000 ASSEMBLIES PER PACKAGE.
- 7

500 ASSEMBLIES PER PACKAGE.
- 8

100 ASSEMBLIES PER PACKAGE.

8	5-554739-3
7	5-554739-2
6, 11	5-554739-1
REELED	554739-1
PACKAGED	PART NUMBER

SUPSD BY 5-554739-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YTP/UTA 8-27-93	TE Connectivity		
DIMENSIONS: mm[INCHES]		CHK C.WHITT 9-15-93			
		APVD TONEY/MCGRATH 9-20-93	NAME		
		PRODUCT SPEC	MODULAR PLUG ASSEMBLY, 8 POSITION, FLAT OVAL CABLE		
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
-		WEIGHT	A2	00779	554739
FINISH		CUSTOMER DRAWING	SCALE	SHEET	REV
-			4:1	1 OF 1	T