




SOCKET OUTLETS ANGLED SURFACE MOUNTING 16 & 32 AMP IP44 SPLASHPROOF
Top Conduit or Rear Cable Entry, Complete with Blanking Plug



A m p s	Pin C o n f i g u r a t i o n	100-130V 50-60Hz List No 	200-250V 50-60Hz List No 	380-415V 50-60Hz List No 	440-460V 50-60Hz List No 	480-500V 50-60Hz List No 	Terminal capacity sq. mm*	Dimensions in mm								Top C o n d u i t E n t r y	R e a r E n t r y	
								A	B	C	C1	E	F	H	D			G
16	2P+E	K9200 YEL 4	K9201 BLU 6	K9202 RED 9			1.5 - 4	91	117	75	54	66	5.5	30	M20	Ø23		
16	3P+E	K9205 YEL 4	K9206 BLU 9	K9207 RED 6	K9208 RED 11	K9209 BLK 7	1.5 - 4	100	132	91	67	79	5.5	30	M20	Ø23		
16	3P+N+E	K9213 YEL 4	K9214 BLU 9	K9215 RED 6	K9216 RED 11		1.5 - 4	104	134	91	67	79	5.5	30	M20	Ø23		
32	2P+E	K9232 YEL 4	K9233 BLU 6				2.5 - 10	118	163	111	72	85	5.5	33	M25	Ø29		
32	3P+E	K9235 YEL 4	K9236 BLU 9	K9237 RED 6		K9238 BLK 7	2.5 - 10	116	163	111	72	85	5.5	33	M25	Ø29		
32	3P+N+E	K9239 YEL 4	K9240 BLU 9	K9241 RED 6	K9242 RED 11		2.5 - 6	121	164	111	72	85	5.5	33	M25	Ø29		
A m p s	Pin C o n f i g u r a t i o n	>50V 100- 300Hz List No 	>50V 300- 500Hz List No 	IS TRAN 50-60Hz List No 	>50-250V d.c List No 		Terminal capacity sq. mm*	Dimensions in mm								Top C o n d u i t E n t r y	R e a r E n t r y	
								A	B	C	C1	E	F	H	D			G
16	2P+E			K9204 GRY 12	K9203 GRY 3		1.5 - 4	91	117	75	54	66	5.5	30	M20	Ø23		
16	3P+E	K9210 GRN 10	K9211 GRN 2				1.5 - 4	100	132	91	67	79	5.5	30	M20	Ø23		
16	3P+N+E		K9252 GRN 2				1.5 - 4	104	134	91	67	79	5.5	30	M20	Ø23		
32	3P+N+E		K9258 GRN 2				2.5 - 10	118	165	111	72	85	5.5	33	M25	Ø29		

 Earth Hour Position

* Solid or Stranded Conductors

Earth Hour Position

* Solid or Stranded Conductors

