

SPECIFICATIONS

Mechanical

Contact Normal Force: 0.03 to 0.05kg
Durability: 10000 Cycles

Electrical


Current Rating: 0.5A
Contact Resistance: 40mΩ max.
Dielectric Withstanding Voltage: 500V AC/1 min.
Insulation Resistance: 1000MΩ min.

Physical





Housing: Thermoplastic, UL 94V-0 rated in Ivory Color
Contact: Copper alloy
Plating: See "ORDERING INFORMATION"
Solder Pad: Copper alloy
Operating Temperature: -55 °C to +85 °C

SIM Card Connector

WL Series
SMT Type
2.54mm [.100"] Pitch
6 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: WL 6 15 A 3 - A01 - TR

SIM Card Connector

Package Type
TR=Tape And Reel

No. of Pos.
6=6 Pos.

Extension Code

Body Height
15=1.50 mm

Contact Plating
3=30μ" Gold

Upper Cover Type
A=Without Upper Cover